

CENTRI[®]

A Fillauer Company



STEPLOCK



Features

- Steplock joints offers the patient security even not though full extension can be reached
- A perfect joint for treating a flexion contracture
- It is easily interchangeable
- The joint has 9 different positions
- Locks in flexion and allows movement in extension

STRAIGHT

Joint Pairs	5 x 12 mm	5 x 16 mm	6 x 16 mm	5 x 19 mm	6 x 19 mm
Straight	692 005 123	692 005 163	692 006 163	692 005 193	692 006 193
Left medial offset	692 005 121	692 005 161	692 006 161	692 005 191	692 006 191
Right medial offset	692 005 120	692 005 160	692 006 160	692 005 190	692 006 190
Double contour	692 005 122	692 005 162	692 006 162	692 005 192	692 006 192
Hip joints	692 005 124	692 005 164	692 006 164	692 005 194	692 006 194

Features

- Interlock is a drop lock alternative that is modular
- Available in five sizes


INTERLOCK



INTERLOCK

Joint Pairs	5 x 12 mm	5 x 16 mm	6 x 16 mm	5 x 19 mm	6 x 19 mm
Straight	692 105 123	692 105 163	692 106 163	692 105 193	692 106 193
Left medial offset	692 105 121	692 105 161	692 106 161	692 105 191	692 106 191
Right medial offset	692 105 120	692 105 160	692 106 160	692 105 190	692 106 190
Double contour	692 105 122	692 105 162	692 106 162	692 105 192	692 106 192
Hip joints	692 105 124	692 105 164	692 106 164	692 105 194	692 106 194

2400 SERIES



Posterior Offset

Minimal Offset

Features

- System joint (bar sold separately)
- Available in single position full extension Unilock, ratcheting Steplock or adjustable stop free motion functions
- Available in Posterior offset and minimal offset

2400 Joint Pairs	Size 5	Size 6	Size 7
UniLock (UL) Minimal Offset (MO)	692 001 013	692 001 014	692 001 015
UniLock (UL) Posterior Offset (PO)	692 001 016	692 001 017	692 001 018
StepLock (SL) Minimal Offset (MO)	692 001 007	692 001 008	692 001 009
StepLock (SL) Posterior Offset (PO)	692 001 010	692 001 011	692 001 012
Free Motion Knee Minimal Offset (MO)	692 001 021	692 001 022	692 001 023
Free Motion Knee Posterior Offset (PO)	692 001 024	692 001 025	692 001 026

Reverse StepLock	Size 5 Left	Size 5 Right	Size 6 Left	Size 6 Right
	692 001 001	692 001 002	692 001 004	692 001 005

Features

- 2400 joints use a 5 mm thick bar that is available in a four piece kit
- Pre-bent distal pairs with 10° medial contour

2400 ACCESSORIES

Alignment fixture	2400 EXTFIX
	692 001 104

BAR KITS

2400 Bar Kits	Size 5	Size 6	Size 7
	692 001 101	692 001 102	692 001 103

Pre-bent distals	Size 5	Size 6	Size 7
UniLock (UL) Minimal Offset (MO)	692 001 033	692 001 034	692 001 035
UniLock (UL) Posterior Offset (PO)	692 001 036	692 001 037	692 001 038
StepLock (SL) Minimal Offset (MO)	692 001 027	692 001 028	692 001 029
StepLock (SL) Posterior Offset (PO)	692 001 030	692 001 031	692 001 032



2755 SERIES



Posterior Offset



Minimal Offset



Reverse Steplock

Features

- Joint with intergrated lower bar & upper system bar
- Low profile
- Extremely high strength
- Low weight
- Available in Steplock, Unilock & Adjustable extension stop free-motion functions
- Available in posterior or minimal offset joint configurations

2755 Joint Kits	Size 5	Size 6	Size 7
UniLock (UL) Minimal Offset (MO)	692 001 049	692 001 050	692 001 051
UniLock (UL) Posterior Offset (PO)	692 001 052	692 001 053	692 001 054
StepLock (SL) Minimal Offset (MO)	692 001 043	692 001 044	692 001 045
StepLock (SL) Posterior Offset (PO)	692 001 046	692 001 047	692 001 048
Free Motion Knee Minimal Offset (MO)	692 001 057	692 001 058	692 001 059
Free Motion Knee Posterior Offset (PO)	692 001 060	692 001 061	692 001 062



Reverse StepLock	Size 5 Left	Size 5 Right	Size 6 Left	Size 6 Right
	692 001 039	692 001 040	692 001 041	692 001 042

RELEASE KITS



IBK-SBK

RBK

UBK

Release Kits	IBK/ SBK	RBK	UBK
	692 000 025	692 000 026	692 000 023

Features

IBK/SBK - For use on Original Series InterLock and StepLock. Made in soldered stainless steel bail.

RBK - For use on Original Series InterLock and StepLock. Made of rod-style bail.

UBK - Only for use on 2400/ 2755 Series UniLock. (Not for StepLock)



LRK

Features

LRK - Lever Release Kit provides a remote operated unlocking mechanism that connects the medial and lateral joints, making it easier to lock and unlock any spring-loaded joint. Easy to fabricate and strong, the LRK is perfect for use on both the InterLock and StepLock knee joints.

Lever Release Kit	LRK 512 Small	LRK 16/19 Large
	692 000 021	692 000 022

Features

- Contour within 1/2" of knee center
- Size 4 for non-ambulatory use
- Size 4.5 for ambulatory use
- Ratcheting Steplock features a built-in lock retainer
- Single position UniLock includes bail
- Unparalleled strength to weight ratio with OTS alloy
- Nickel plated finish for durability
- **Upper extremity kit** is available in steplock size 4
- Elbow forward extension ratcheting
- Reverse flexion ratcheting for positioning
- Wrist ratcheting from 90° plantar flexion to 30° dorsi flexion

CLOSE CONTOUR

StepLock & UniLock	Size 4	Size 4.5
StepLock	692 001 063	692 001 065
UniLock	692 001 064	692 001 066

Close contour Upper extremity Kits	Right Lateral	Left Lateral
Wrist	692 001 072	692 001 071
Extension Elbow	692 001 068	692 001 067
Reverse (flexion) Elbow	692 001 070	692 001 069



INTEGRATED ANKLE

Features


- Double action integrated ankle has the ability to spring load the posterior channel providing dynamic assist for dorsi flexion.
- The integrated Dorsi flexion assist (DFA) is lightweight & has a low profile
- Adjustable range of motion has two adjustment screws, one to limit plantarflexion & one to limit dorsiflexion



Double action



Dorsi-flexion assist



Adjustable range of motion

Thermoformable, Alloy Joint pairs	5 Child (small)	6 Youth (medium)	7 Adult (large)
Double action	692 100 003	692 100 002	692 100 001
Dorsi-Flexion Assist	692 200 003	692 200 002	692 200 001
Adjustable range of motion	692 200 005	NOT AVAILABLE	692 200 004

Modular, Steel Joint pairs	Size 5 (12 mm slot)	Size 6 (16 mm slot)	Size 7 (19 mm slot)
Double action Square slot	692 200 006	692 200 007	692 200 008
Adjustable range of motion Square bar	692 200 009	692 200 010	692 200 011

INTEGRATED ANKLE

Modular, Alloy Joint pairs	Size 5 (12 mm slot)	Size 6 (16 mm slot)	Size 7 (19 mm slot)
Double action Square bar	692 200 012	692 200 013	692 200 014
Adjustable range of motion Square bar	692 200 015	692 200 016	692 200 017

CE

DOUBLE ACTION ANKLE

Features

- Square bar slot for easy finishing
- Easily converts from inside to outside bar slot
- Can be attached with screws or rivets
- Available in 5/8" bar slot for adult use
- Stainless steel

Stainless steel
Double action ankle

692 200 018



CE

STIRRUPS



Split tail Pairs	Child (small)	Youth (medium)	Adult (large)
Double action	692 000 030	692 000 031	692 000 032

Solid stirrup Wide tongue	Child (small)	Adult (large)
	692 000 044	692 000 046
	692 000 045	692 000 041
	692 000 040	692 000 042
	Not available	692 000 047

Ankle Lamination Kits (stirrups & bars)	Child 12 mm (small)	Youth 16 mm (medium)	Adult 19 mm (large)
Alloy	692 200 020	692 200 022	692 200 024
Steel	692 200 019	692 200 021	692 200 023

Features

- The unique “Y” shape of the split-tail is perfectly suited for use in plastic shoe insert configurations
- Solid stirrup comes in many sizes
- Choose between Adult & Child thickness and then choose length.
- The Ankle lamination kits comes with one pair of ankle joints, one pair of uprights, stirrup, alignment rod and dummy plates



DRILL FIXTURE & BAR STOCK

Features

- Comes with spot drill and drill/counter-sink combo bits for precise and accurate holes every time
- Drills and countersinks all of our bar combinations, knee and ankle

Drill Fixture	
Drill fixture & bits	692 001 105



Bar stock	5mm x 12 mm	5 mm x 16 m	5 mm x 19 mm
18.3 cm length bar stock	692 001 106	692 001 107	692 001 108

Step 1
Slide bar into appropriate slot and spot or mark hole alignment with drill bit

Step 2
Punch through and countersink in one step with drill/ counter-sink combo bit

Step 3
Clean off your new up-rights and attach them to any OTS joint



INFRARED OVEN PDQ -BT-1

Features

- Aluminium & stainless steel construction
- Four 650W infrared emitters
- Interior light
- Double pane viewing window
- Programmable digital temperature controller
- Tray with a fitted Teflon cover
- Weight (uncrated) 113 kg
- Full 1 year warranty



Dimensions:

Interior:

96 cm wide x 76 cm deep x 15 cm high

Exterior:

106 cm wide x 109 cm deep x 51 cm high
(112 cm high with legs)

Electrical requirements:

230 V, 20 amp, single phase

Article number:

692 900 025

INFRARED OVEN

PDQ -BT-3



Features

- Aluminium & stainless steel construction
- Four 650W infrared emitters on top & four on bottom
- Interior light
- Two double pane viewing window
- Programable digital temperature controller
- Fitted teflon sheet for tray
- Full 1 year warranty

Dimensions:

Interior:

71 cm wide x 101 cm deep x 61 cm high

Exterior:

81 cm wide x 124 cm deep x 155 cm high

Electical requirements:

230 V, 30 amp, single phase

Article number:

692 900 026

INFRARED OVEN ROLLABOUT



	Article number
5A	692 900 020
6B	692 900 021
7C	692 900 022
8E	692 900 024

Features

- Aluminium & stainless steel construction
- Four 650W infrared emitters (1000 W on 8E)
- Interior light
- Two double pane viewing window
- Programmable digital temperature controller
- Tray includes a fitted teflon cover
- Full 1 year warranty

Dimensions:

Interior:

- 5/A - 97 cm wide x 79 cm deep x 46 cm high
- 6/B - 91 cm wide x 130 cm deep x 46 cm high
- 7/C - 122 cm wide x 130 cm deep x 46 cm high
- 8/E - 152 cm wide x 122 cm deep x 46 cm high

Exterior:

- 5/A - 89 cm deep x 124 cm wide x 122 cm high
- 6/B - 140 cm deep x 120 cm wide x 122 cm high
- 7/C - 140 cm deep x 150 cm wide x 122 cm high
- 8/E - 132 cm deep x 178 cm wide x 122 cm high

Electical requirements:

230 V, single phase

INFRARED OVEN PDQ -8D:2

Features

- Aluminium & stainless steel construction
- Four 650W infrared emitters on top & four on bottom
- Interior light
- Two double pane viewing window
- Programmable digital temperature controller
- Fitted teflon sheet for tray
- Full 1 year warranty



Dimensions:

Interior:

99 cm wide x 127 cm deep x 46 cm high/ each
203 cm wide x 127 cm deep x 46 cm high/ tray
combined

Exterior:

81 cm wide x 125 cm deep x 155 cm high

Electical requirements:

230 V, 30 amp, single phase

Article number:

692 900 023

INFRARED OVEN PDQ -PO-2

Features

- Aluminium & stainless steel construction
- Four 1000 W infrared emitters on top & four on bottom
- Interior light
- Two double pane viewing window
- Programmable digital temperature controller
- Fitted teflon sheet for tray
- Rollabout tray/ rack
- Full 1 year warranty



Dimensions:

Interior:

127 cm wide x 91 cm deep x 51 cm high

Exterior:

153 cm wide x 102 cm deep x 135 cm high

Electical requirements:

230 V, 50 amp, single phase

Article number:

692 900 027

MINI MOBILE OVEN



Features

- Light; weighing less than 14 kg
- Heats up to 77° Celcius
- Easy to transport with wheels and handle
- Interior dimensions: 66 cm x 66 cm
- Exterior dimensions: 74 cm wide x 80 cm deep x 13 cm high

Article number:

692 900 028



MAXI MOBILE OVEN



Features

- Portable with wheels and handle
- Plugs into standard 230 V outlets
- Heats up to 77° Celcius
- Weighs less than 18 kg
- Interior dimensions: 66 cm x 97 cm
- Exterior dimensions: 102 cm wide x 80 cm deep x 13 cm high

Article number:

692 900 029



PLASTIC RACK



CE

Features

- The plastic rack stores all of your sheet plastic
- Available in two sizes:
76 cm high x 132 cm wide x 81 cm deep
or 76 cm high x 132 cm wide x 112 cm deep

Article number:

LARGE - 692 900 037
SMALL - 692 900 038

MOLD LIBRARY

Features

- Get the casts up off the floor
- Dimension:
213 cm high x 92 cm wide x 41 cm deep

Article number:

692 900 035

CE



OTS Cross Reference Chart

OTS no. - Centri no.

SL 512 KS - 692 005 123
 SL 512 KL - 692 005 121
 SL 512 KR - 692 005 120
 SL 512 KB - 692 005 122
 SL 512 H - 692 005 124
 SL 516 KS - 692 005 163
 SL 516 KL - 692 005 161
 SL 516 KR - 692 005 160
 SL 516 KB - 692 005 162
 SL 516 H - 692 005 164
 SL 519 KS - 692 005 193
 SL 519 KL - 692 005 191
 SL 519 KR - 692 005 190
 SL 519 KB - 692 005 192
 SL 519 H - 692 005 194
 SL 616 KS - 692 006 163
 SL 616 KL - 692 006 161
 SL 616 KR - 692 006 160
 SL 616 KB - 692 006 162
 SL 616 H - 692 006 164
 SL 619 KS - 692 006 193
 SL 619 KL - 692 006 191
 SL 619 KR - 692 006 190
 SL 619 KB - 692 006 192
 SL 619 H - 692 006 194
 IL 512 KS - 692 105 123
 IL 512 KL - 692 105 121
 IL 512 KR - 692 105 120
 IL 512 KB - 692 105 122
 IL 512 H - 692 105 124
 IL 516 KS - 692 105 163
 IL 516 KL - 692 105 161
 IL 516 KR - 692 105 160
 IL 516 KB - 692 105 162
 IL 516 H - 692 105 164
 IL 519 KS - 692 105 193
 IL 519 KL - 692 105 191
 IL 519 KR - 692 105 190
 IL 519 KB - 692 105 192
 IL 519 H - 692 105 194
 IL 616 KS - 692 106 163
 IL 616 KL - 692 106 161
 IL 616 KR - 692 106 160
 IL 616 KB - 692 106 162
 IL 616 H - 692 106 164
 IL 619 KS - 692 106 193
 IL 619 KL - 692 106 191
 IL 619 KR - 692 106 190
 IL 619 KB - 692 106 1902
 IL 619 H - 692 106 194

OTS no. - Centri no.

2400 ULM05K - 692 001 013
 2400 ULPO5K - 692 001 016
 2400 SLMO5K - 692 001 007
 2400 SLPO5K - 692 001 010
 2400 FM5K - 692 001 021
 2400 PO5K - 692 001 024
 2400 R-SLMO5L - 692 001 001
 2400 ULM06K - 692 001 014
 2400 ULPO6K - 692 001 017
 2400 SLMO6K - 692 001 008
 2400 SLPO6K - 692 001 011
 2400 FM6K - 692 001 022
 2400 PO6K - 692 001 025
 2400 R-SLMO5RL - 692 001 002
 2400 ULM07K - 692 001 015
 2400 ULPO7K - 692 001 018
 2400 SLMO7K - 692 001 009
 2400 SLPO7K - 692 001 012
 2400 FM7K - 692 001 023
 2400 PO7K - 692 001 026
 2400 R-SLMO6L - 692 001 004
 2400 R-SLMO6R - 692 001 005
 2400 ULM05-CK - 692 001 033
 2400 ULPO5-CK - 692 001 036
 2400 SLMO5-CK - 692 001 027
 2400 SLPO5-CK - 692 001 030
 2400 ULM06-CK - 692 001 034
 2400 ULPO6-CK - 692 001 037
 2400 SLMO6-CK - 692 001 028
 2400 SLPO6-CK - 692 001 031
 2400 ULM07-CK - 692 001 035
 2400 ULPO7-CK - 692 001 038
 2400 SLMO7-CK - 692 001 029
 2400 SLPO7-CK - 692 001 032
 2755 ULM05K - 692 001 049
 2755 ULPO5K - 692 001 052
 2755 SLMO5K - 692 001 043
 2755 SLPO5K - 692 001 046
 2755 FMMO5K - 692 001 057
 2755 FMPO5K - 692 001 060
 2755 R-SLMO5L - 692 001 039
 2755 R-SLMO5R - 692 001 040
 2755 R-SLMO6L - 692 001 041
 2755 R-SLMO6R - 692 001 042
 2755 ULM06K - 692 001 050
 2755 ULPO6K - 692 001 053
 2755 SLMO6K - 692 001 044
 2755 SLPO6K - 692 001 047
 2755 FMMO6K - 692 001 058
 2755 FMPO6K - 692 001 061
 2755 ULM07K - 692 001 051
 2755 ULPO7K - 692 001 054
 2755 SLMO7K - 692 001 045
 2755 SLPO7K - 692 001 048
 2755 FMMO7K - 692 001 059
 2755 FMPO7K - 692 001 062

OTS no. - Centri no.

CC4SL - 692 001 063
 CC4UL - 692 001 064
 CC4.5SL - 692 001 065
 CC4.5UL - 692 001 066
 CC4WSL-R - 692 001 072
 CC4ESL-R - 692 001 068
 CC4RSL-R - 692 001 070
 CC4WSL-L - 692 001 071
 CC4ESL-L - 692 001 067
 CC3RSL-L - 692 001 069
 IACHDA-AL - 692 100 003
 IACHDF-AL - 692 200 003
 IASMARM-AL - 692 200 005
 IAYTHDA-AL - 692 100 002
 IAYTHDF-AL - 692 200 002
 IAADDA-AL - 692 100 001
 IAADDF-AL - 692 200 001
 IALGARM-AL - 692 200 004
 IA12-EU - 692 200 006
 IA12ARM-EU - 692 200 009
 IA16-EU - 692 200 007
 IA16ARM-EU - 692 200 010
 IA19-EU - 692 200 008
 IA19ARM-EU - 692 200 011
 IA12-AL - 692 200 012
 IA12ARM-AL - 692 200 015
 IA12-AL - 692 200 013
 IA12ARM-AL - 692 200 016
 IA12-AL - 692 200 014
 IA12ARM-AL - 692 200 017
 SLU2220-A - 692 200 018
 IARCHDAST - 692 000 030
 IARYTHDAST - 692 000 031
 IARADDAST - 692 000 032
 STWTDA6.5CH - 692 000 044
 STWTDA7.25CH - 692 000 045
 STWTDA8CH - 692 000 040
 STWTDA8.75 - 692 000 046
 STWTDA9.5 - 692 000 041
 STWTDA10.25 - 692 000 042
 STWTDA11 - 692 000 047
 IA12AL-LK - 692 200 020
 IA12LK - 692 200 019
 IA16-ALLK - 692 200 022
 IA16LK - 692 200 021
 IA19-ALLK - 692 200 024
 IA19LK - 692 200 023
 2400DF - 692 001 105
 BARSTOCK512 - 692 001 106
 BARSTOCK516 - 692 001 107
 BARSTOCK519 - 692 001 108

OTS no. - Centri no.

5A - 692 900 020
 6B - 692 900 021
 7C - 692 900 022
 8E - 692 900 024
 8D2 - 692 900 023
 BT1 - 692 900 025
 BT3 - 692 900 026
 PO2 - 692 900 027
 MINI - 692 900 028
 MAXI - 692 900 029
 MOLD LIBRARY - 692 900 035
 RACK LARGE - 692 900 037
 RACK SMALL - 692 900 038



A Fillauer Company